


Art. 039

Trójnik redukcyjny krótki

Strona 1/2




DN	D1	D2	D3	D4	L	L1	Waga (kg)
15/10	15	18	9	12	70	10	0,040
20/10	19	22	9	12	80	12	0,070
20/15	19	22	15	18	80	12	0,060
25/10	25	28	9	12	100	16	0,110
25/15	25	28	15	18	100	16	0,100
25/20	25	28	19	22	100	16	0,090
32/15	31	24	15	18	110	20,5	0,130
32/20	31	34	19	22	110	20,5	0,130
32/25	31	34	25	28	110	20,5	0,130
40/15	37	40	15	18	120	23	0,160
40/20	37	40	19	22	120	23	0,160
40/25	37	40	25	28	120	23	0,160
40/32	37	40	31	34	120	23	0,150
50/20	49	52	19	22	140	29	0,260
50/25	49	52	25	28	140	29	0,240
50/32	49	52	31	34	140	29	0,250
50/40	49	52	37	40	140	29	0,230

Art. 039

Trójnik redukcyjny krótki

Strona 2/2



DN	D1	D2	D3	D4	L	L1	Waga (kg)
65/25	66	70	25	28	160	39	0,520
65/32	66	70	31	34	160	39	0,520
65/40	66	70	37	40	160	39	0,510
65/50	66	70	49	52	160	39	0,520
80/25	81	85	25	28	180	47	0,720
80/32	81	85	31	34	180	47	0,700
80/40	81	85	37	40	180	47	0,700
80/50	81	85	49	52	180	47	0,690
80/65	81	85	66	70	180	47	0,680
100/25	100	104	25	28	200	58	0,960
100/32	100	104	31	34	200	58	0,960
100/40	100	104	37	40	200	58	0,950
100/50	100	104	49	52	200	58	0,940
100/65	100	104	66	70	200	58	0,950
100/80	100	104	81	85	200	58	0,950
125/80	125	129	81	85	374	71,5	2,170
125/100	125	129	100	104	374	71,5	2,140
150/80	150	154	81	85	450	87	3,170
150/100	150	154	100	104	450	87	3,140
150/125	150	154	125	129	450	87	3,070